

50 mm Offset Positioner, Solid Round Conductor



FEATURES

Positioning clamps with 50 mm (1.97") offset for use with solid round conductors, including nVent ERICO Cu-Bond Round Conductor

For use with copper-bonded, copper, or stainless steel solid conductors

SPECIFICATIONS

Table 1/2


Catalog Number	Material	Width 1 (W1)	Width 2 (W2)	Height 1 (H1)	Height 2 (H2)	Depth (D)
CSS1314050	Stainless Steel 18-8 (EN 1.4305), Stainless Steel 316 (EN 1.4401)	100 mm	80 mm	65mm	50mm	17mm

Table 2/2

Catalog Number	nVent ERICO Cu-Bond Conductor	Unit Weight	Complies With
CSS1314050	CBSC13, CBSC14	0.01 kg	IEC® 62561-4

ADDITIONAL PRODUCT DETAILS

IEC compliance is valid only for nVent ERICO Cu-Bond Conductors listed.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

