

Inner Doors, ADI



Displays and indicators can be mounted on a surface within the enclosure while covering other components, and preventing unauthorized access.

FEATURES

Description: For controls, meters, lamps, etc. Hinges can be mounted to allow left or right hand opening. Lock double-bit 3 mm insert; 700 mm high doors and above have 2 locks. Usable depth between inner and external door: 35 mm. Adjustable depth position with AMG accessory. Workable area: H-55, W- 108. 19" version available on request. Machining is required for stainless steel enclosures.

Material: Door 1.5 mm mild steel, vertical top and bottom profiles 2 mm mild steel.

Finish: RAL 7035 structured powder coating.

Protection: IP 2XC.

Pack quantity: Inner door, two vertical profiles, top and bottom profiles and mounting accessories.

Material: Mild Steel
Finish: Powder Coated
Color: Light Gray
Color Code: RAL 7035
Thickness: 1.5mm

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Door Size	Latch Quantity
ADI04030R5	ADI04030R5	374mm	261mm	71mm	345 x 192mm	1
ADI04040R5	ADI04040R5	374mm	374mm	71mm	345 x 292mm	1
ADI04050R5	ADI04050R5	374mm	461mm	71mm	345 x 392mm	1
ADI04060R5	ADI04060R5	374mm	561mm	71mm	345 x 492mm	1
ADI05030R5	ADI05030R5	474mm	261mm	71mm	445 x 192mm	1
ADI05040R5	ADI05040R5	474mm	374mm	71mm	445 x 292mm	1
ADI05050R5	ADI05050R5	474mm	461mm	71mm	445 x 392mm	1
ADI06040R5	ADI06040R5	574mm	374mm	71mm	545 x 292mm	1
ADI06050R5	ADI06050R5	574mm	461mm	71mm	545 x 392mm	1

Catalog Number	Article Number	Height	Width	Depth	Door Size	Latch Quantity
ADI06060R5	ADI06060R5	574mm	561mm	71mm	545 x 492mm	1
ADI06080R5	ADI06080R5	574mm	761mm	71mm	545 x 692mm	1
ADI07050R5	ADI07050R5	674mm	461mm	71mm	645 x 392mm	2
ADI08040R5	ADI08040R5	774mm	374mm	71mm	745 x 292mm	2
ADI08060R5	ADI08060R5	774mm	561mm	71mm	745 x 492mm	2
ADI08080R5	ADI08080R5	774mm	761mm	71mm	745 x 692mm	2
ADI10060R5	ADI10060R5	974mm	561mm	71mm	945 x 492mm	2
ADI10080R5	ADI10080R5	974mm	761mm	71mm	945 x 692mm	2
ADI12060R5	ADI12060R5	1174mm	561mm	71mm	1145 x 492mm	2
ADI12080R5	ADI12080R5	1174mm	761mm	71mm	1145 x 692mm	2

ADDITIONAL PRODUCT DETAILS

Not suitable for AFS.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

