

Varistar CP Cabeling Rack



Welded steel frame for high static load requirements.
Prepared for high cable densities and 19" integration.

FEATURES

Preconfigured, ready to use cabinet

Static load-carrying capacity up to 1600 kg

Ingress protection class IP 20

Installation of different Networking equipment possible

Integrated vertical and horizontal cable management

Can be easily integrated into aisle containment system

Frame Material: Steel

Material: Steel

Product Type: Rack

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Height	Cladding Material	Frame Color	Height	Frame Color Code	Cladding Color
10630-027	42U	Steel	Black Grey	2000mm	RAL 7021	Black Grey
10630-028	42U	Steel	Black Grey	2000mm	RAL 7021	Black Grey

Table 2/2

Catalog Number	Width	Depth	Static Load	Cladding Color Code	Package Quantity	Dynamic Load	Finish
10630-027	800mm	1200mm	1600kg	RAL 7021	1	1000kgf	Powder Coated
10630-028	800mm	1200mm	1600kg	RAL 7021	1	1000kgf	Powder Coated

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

