

BC-M Conduit to Beam Clamp, 14–18 mm OD, 16 mm Max Flange



CATALOG NUMBER

EBC6M

FEATURES

- Easy installation to beam flanges
- Eliminates offset bending conduit
- Conduit clip rotates 360 degrees

PRODUCT ATTRIBUTES

Article Number: 172580

Material: Spring Steel

Finish: nVent CADDY Armour

Outer Diameter (OD): 14 - 18 mm

Flange Thickness (FT): 16 mm Max

Torque (TQ): 3 N·m

Static Load: 450N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500

