

C-Channel U-Shaped Washer, 28 mm x 15 mm, 10.5 mm Hole

CATALOG NUMBER

PLNE010

FEATURES

U-shaped wrap around washer

For use with C-Profiles



PRODUCT ATTRIBUTES

Article Number: 588250

Material: Steel

Finish: Electrogalvanized

A: 28 mm

B: 30 mm

C: 15 mm

Thickness (T): 2 mm

Hole Size (HS): 10.5 mm

Channel Type: E0;E0L



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

