

Quick Strut Nut with Stud, M10 Rod, 22 mm



CATALOG NUMBER

QSNM10040EG

FEATURES

Provides fast universal attachment of threaded rod and hardware to standard strut profiles

Pre-assembled slide nut ready to use out of the box

Spring retains assembly in place until hardware is tightened

PRODUCT ATTRIBUTES

Article Number: 592922

Material: Steel

Finish: Electrogalvanized

Rod Size (RS): 10

Length 1 (L1): 22 mm

Length 2 (L2): 50 mm

A: 8 mm

B: 4 mm

C: 41 mm

Torque (TQ): 55 N·m

Static Load 1 (F1): 4400N

Static Load 2 (F2): 4400N

Static Load 3 (F3): 4900N

ADDITIONAL PRODUCT DETAILS

Static Load 1 represents 1.5 mm strut channel thickness. Static Load 2 represents 2.0 mm strut channel thickness. Static Load 3 represents 2.5 mm strut channel thickness.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

