

Wire Basket Tray Drop Out



The nVent CADDY Wire Basket Tray Drop Out is a versatile solution for creating cable management exits in cable tray. By acting as a wire funnel, the Drop Out enables cables to easily drop vertically from the tray while ensuring proper support and protecting the bend radius at the exit point. The tool-free design allows installers to drop the component into place on the wire basket tray while the side prongs hold it firmly in place. Whether contractors are working with multi-tier assemblies or side-by-side configurations, the Drop Out offers an aesthetic and efficient way to manage cable transitions, without compromising on performance or accessibility.

FEATURES

Designed for center cable tray dropouts

Conducive to creating both multi-tier tray and side-by-side assemblies

Easily cut to fit around the wire basket tray for retrograde cable installations

Ensures the natural bend radius of the cable is protected

Stackable for multiple adjoining dropouts

Reusable and tool-free—easy-to-install, easy-to-remove


Material: ABS, UL-V0 rated

Finish: Pregalvanized

SPECIFICATIONS

Catalog Number	Height (H)	Width (W)	Length (L)	Unit Weight
WBTCBLDO	28.6 mm	58.74 mm	90.5mm	0.05 kg
WBTCBLDO4	28.6 mm	109.3 mm	92.08mm	0.01 kg
WBTCBLDO6	29.4 mm	158 mm	210.85mm	0.02 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

