

# Wire Basket Tray L Bracket



The nVent CADDY Wire Basket Tray L Bracket delivers a clean, space-efficient solution for supporting wire basket trays in data application environments. Unlike multi-tier or ceiling-mounted supports, the L Bracket is optimized for single-plane, wall-mounted runs, making it ideal for installations where floor space is limited or ceiling access is restricted.

Its low-profile design simplifies installation without compromising strength. The bracket's side-load access allows for seamless cable placement, even in retrofit scenarios. At nVent CADDY, we are committed to providing you with innovative product offerings that empower you and solve your problems, not matter how complex.

## FEATURES

Easy-to-use quick connect feature

Designed to be used with the nVent CADDY Wire Basket Tray Washer Support and nVent CADDY Wire Basket Tray Ground Splice

Utilize with the nVent CADDY Wire Basket Tray C Bracket for multi-tier cable tray runs


**Material:** Steel  
**Finish:** Electrogalvanized



## SPECIFICATIONS

| Catalog Number | Color | Height (H) | Width (W) | Length (L) | Hole Size (HS) | Unit Weight |
|----------------|-------|------------|-----------|------------|----------------|-------------|
| WBTLBRKT12     |       | 127 mm     | 41.4 mm   | 350.52mm   | 7.16 mm        | 0.712 kg    |
| WBTLBRKT12BA   | Black | 127 mm     | 41.4 mm   | 198.12mm   | 7.16 mm        | 0.712 kg    |
| WBTLBRKT4      |       | 127 mm     | 41.4 mm   | 96.52mm    | 7.16 mm        | 0.395 kg    |
| WBTLBRKT4BA    | Black | 127 mm     | 41.4 mm   | 452.12mm   | 7.16 mm        | 0.395 kg    |
| WBTLBRKT6      |       | 127 mm     | 41.4 mm   | 452.12mm   | 7.16 mm        | 0.476 kg    |
| WBTLBRKT6BA    | Black | 127 mm     | 41.4 mm   | 502.92mm   | 7.16 mm        | 0.476 kg    |
| WBTLBRKT8      |       | 127 mm     | 41.4 mm   | 553.72mm   | 7.16 mm        | 0.553 kg    |
| WBTLBRKT8BA    | Black | 127 mm     | 41.4 mm   | 553.72mm   | 7.16 mm        | 0.553 kg    |

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

