


# Wire Basket Tray Polymer Insert



The nVent CADDY Wire Basket Tray Polymer Insert utilizes a flame-retardant polymer to envelop the entire tray- providing bottom, side and cover protection. Available options include a flat bottom or a prescored version to the tray depth for coverage of the bottom and sides.

## FEATURES

Standard black finish for use with divider posts

Polymer insert rolls into the tray bottom

Multiple color options to coordinate with cable tray selection


**Color:** Black  
**Material:** Polymer

## SPECIFICATIONS

| Catalog Number | Height (H) | Width (W) | Length (L) | Sides Included | Unit Weight |
|----------------|------------|-----------|------------|----------------|-------------|
| WBTFORM06BA    |            | 143 mm    | 3048mm     | No             | 0.03 kg     |
| WBTFORM08BA    |            | 193.8 mm  | 3048mm     | No             | 0.04 kg     |
| WBTFORM12BA    |            | 295.4 mm  | 3048mm     | No             | 0.06 kg     |
| WBTFORM18BA    |            | 447.8 mm  | 3048mm     | No             | 0.09 kg     |
| WBTFORM24BA    |            | 600.2 mm  | 3048mm     | No             | 0.12 kg     |
| WBTFORM2X12BA  | 50.8 mm    | 295.4 mm  | 3048mm     | Yes            | 0.08 kg     |
| WBTFORM2X18BA  | 50.8 mm    | 447.8 mm  | 3048mm     | Yes            | 0.11 kg     |
| WBTFORM2X24BA  | 50.8 mm    | 600.2 mm  | 3048mm     | Yes            | 0.14 kg     |
| WBTFORM2X4BA   | 50.8 mm    | 92.2 mm   | 3048mm     | Yes            | 0.04 kg     |
| WBTFORM2X6BA   | 50.8 mm    | 143 mm    | 3048mm     | Yes            | 0.05 kg     |
| WBTFORM2X8BA   | 50.8 mm    | 193.8 mm  | 3048mm     | Yes            | 0.06 kg     |
| WBTFORM4X12BA  | 101.6 mm   | 295.4 mm  | 3048mm     | Yes            | 0.1 kg      |
| WBTFORM4X16BA  | 101.6 mm   | 397 mm    | 3048mm     | Yes            | 0.12 kg     |
| WBTFORM4X18BA  | 101.6 mm   | 447.8 mm  | 3048mm     | Yes            | 0.13 kg     |
| WBTFORM4X24BA  | 101.6 mm   | 600.2 mm  | 3048mm     | Yes            | 0.16 kg     |
| WBTFORM4X4BA   | 101.6 mm   | 92.2 mm   | 3048mm     | Yes            | 0.06 kg     |

| Catalog Number | Height (H) | Width (W) | Length (L) | Sides Included | Unit Weight |
|----------------|------------|-----------|------------|----------------|-------------|
| WBTFORM4X6BA   | 101.6 mm   | 143 mm    | 3048mm     | Yes            | 0.07 kg     |
| WBTFORM6X12BA  | 152.4 mm   | 295.4 mm  | 3048mm     | Yes            | 0.12 kg     |
| WBTFORM6X18BA  | 152.4 mm   | 447.8 mm  | 3048mm     | Yes            | 0.16 kg     |
| WBTFORM6X24BA  | 152.4 mm   | 600.2 mm  | 3048mm     | Yes            | 0.18 kg     |

### DIAGRAMS



### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

#### North America

+1.800.753.9221  
 Option 1 – Customer Care  
 Option 2 – Technical Support

#### Europe

Netherlands:  
 +31 800-0200135  
 France:  
 +33 800 901 793

#### Europe

Germany:  
 800 1890272  
 Other Countries:  
 +31 13 5835404

#### APAC

Shanghai:  
 + 86 21 2412 1618/19  
 Sydney:  
 +61 2 9751 8500

