

KP T-Bolt for C-Channel E0/E0L/E1, M8 Screw, 30 mm Screw



CATALOG NUMBER

KP2708030

FEATURES

For use with C-Profiles

Pre-mounted with large washer and nut

PRODUCT ATTRIBUTES

Article Number: 590076

Channel Type: E0;E0L;E1

Material: Steel

Finish: Electrogalvanized

Screw Diameter (Sc): 8

Screw Length (L): 30mm

A: 25 mm

B: 14 mm

ADDITIONAL PRODUCT DETAILS

Sliding force F2 is limited to 600 N for all types of Nuts and T-Bolts for C-channel System.

Nuts and T-Bolts for C-channel System	
C-Channel Type	Pullout Force F1
E0	1300 N
E0L	800 N
E1	1900 N

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

