

HK Cable Snap Clip



FEATURES


Provides support for low voltage cables

Attaches easily to beam

Material: Steel
Finish: Electrogalvanized

SPECIFICATIONS

Catalog Number	Article Number	Flange Thickness (FT)	Outer Diameter (OD)
HK25	187440	1.5 - 4.5 mm	4.2 - 6.5 mm
HK48	187450	4 - 8 mm	4.2 - 6.5 mm
HK811	187460	8 - 11 mm	4.2 - 6.5 mm



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

