

Wire Basket Tray PreForm Tee



The nVent CADDY Wire Basket Tray PreForm Tee is a precision-engineered solution designed to streamline cable tray installations when routing cabling in two or three different directions. With its pre-galvanized steel base and interlocking polymer sidewalls, the PreForm Tee delivers a clean, consistent, and tool-free installation experience.

Additionally, the PreForm Tee significantly reduces installation time by eliminating the need for field cutting or job site configuration. This translates into improved productivity and increased efficiency, especially in retrofit scenarios where flexibility is critical.

FEATURES

Multiple color options to coordinate with cable tray selection

Flame-retardant polymer rails ensure the safety of high-performance cabling

Routes cable systems in two or three directions

Provides a clean bend radius and helps to protect the natural bend radius of varying cable systems

Material: Steel
Finish: Pregalvanized; Polyurethane



SPECIFICATIONS

Table 1/2

Catalog Number	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)	Radius (R)	Unit Weight
WBTT2X12		50.8 mm	515.62 mm	711.2mm	19.05 mm	94.64mm	2.722 kg
WBTT2X12BA	Black	50.8 mm	515.62 mm	711.2mm	19.05 mm	94.64mm	2.722 kg
WBTT2X18		50.8 mm	668.02 mm	863.6mm	19.05 mm	94.64mm	4.536 kg
WBTT2X18BA	Black	50.8 mm	668.02 mm	863.6mm	19.05 mm	94.64mm	4.536 kg

Catalog Number	Color	Height (H)	Width (W)	Length (L)	Hole Size(HS)	Radius(R)	UnitWeight
WBTT2X24		50.8 mm	817.88 mm	1013.46m m	19.05 mm	94.64mm	7.257 kg
WBTT2X24BA	Black	50.8 mm	817.88 mm	1013.46mm	19.05 mm	94.64mm	7.257 kg
WBTT2X4		50.8 mm	317.5 mm	513.08mm		94.64mm	0.454 kg
WBTT2X4BA	Black	50.8 mm	317.5 mm	513.08mm		94.64mm	0.454 kg
WBTT2X6		50.8 mm	365.76 mm	561.34mm		94.64mm	1.361 kg
WBTT2X6BA	Black	50.8 mm	365.76 mm	561.34mm		94.64mm	1.361 kg
WBTT2X8		50.8 mm	416.56 mm	612.14mm		94.64mm	1.814 kg
WBTT2X8BA	Black	50.8 mm	416.56 mm	612.14mm		94.64mm	1.814 kg
WBTT6X6		152.39999999999998 mm					
WBTT2X4S4		50.8 mm					
WBTT4X12		101.6 mm					
WBTT4X12BA	Black	101.6 mm					
WBTT4X18		101.6 mm					
WBTT4X18BA	Black	101.6 mm					
WBTT4X24		101.6 mm					
WBTT4X24BA	Black	101.6 mm					

Table 2/2

Catalog Number	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)	Radius (R)	Unit Weight
WBTT4X4		101.6 mm					
WBTT4X4BA	Black	101.6 mm					
WBTT4X6		101.6 mm					
WBTT4X6BA	Black	101.6 mm					
WBTT6X12		152.4 mm					
WBTT6X12BA	Black	152.4 mm					
WBTT6X18		152.4 mm					
WBTT6X18BA	Black	152.4 mm					
WBTT6X24		152.4 mm					
WBTT6X24BA	Black	152.4 mm					
WBTT6X36		152.4 mm					

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

