



		$\Delta \sigma_{\perp}^{*}$ can be simplified: $\Delta \sigma_{\perp}^{*} = \text{simplification not recommended}$			
 Longitudinal A-B		-	+	+	neutral for support
	 Transverse C-D	+	neutral for flexion (no compression)	neutral for flexion and neutral for compression	
 Longitudinal E-F		neutral for flexion	neutral for flexion		
	 Transverse G-H	+	+	-	-
side panel    		light = 1	flexion = 2	shear = 3	support = 4

34566-763

FEATURES

Aluminum extrusion, anodized finish, conductive contact surface



Works With: Subracks

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff

