


# Rooftop Pyramid Equipment Support Kit, 6 Post Base, 2172 mm



## CATALOG NUMBER

**PEK6B**

## FEATURES

Kit includes post-base assemblies, frame and equipment-support clamps

Assembles and adjusts to size and height in minutes by one person with one tool

Innovative crossbar and equipment-support clamps enable quick assembly

Integral foam pad provides gentle interface for all roof types

Hot-dip galvanized and UV stabilized for long lasting performance

Assembled support can be lifted as one unit and easily relocated



## PRODUCT ATTRIBUTES

Article Number: 360427

Material: Steel;Polypropylene;Polyethylene

Finish: Hot-Dip Galvanized

Temperature: -34 to 54.4 °C

Height (H): 305 - 457 mm

Length (L): 2172mm

Post Base (A): 314 mm x 6 pc

Square Tube (B): 1981 mm x 2 pc

Cross Bar Assembly (C): 1232 mm x 4 pc

Width (W): 1588 mm

Surface Area: 0.56m<sup>2</sup>

Unit Weight: 56 kg



Ultimate Static Load (F): 9960N

Static Load Safety Factor: 3:1

## ADDITIONAL PRODUCT DETAILS

Static load must be stable and uniformly distributed across frame.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

### Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

### Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

### APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

[nVent.com/ENDD1](http://nVent.com/ENDD1)

