

# nVent CADDY Speed Link SLK with Y-Toggle



## FEATURES

Complete system includes wire, locking device and two pre-assembled toggle end fittings

Attaches to clearance holes in a variety of structures or hanging devices

Ideal for supporting lighting fixtures


**Material:** Steel;Zinc Alloy;Polypropylene  
**Finish:** Electrogalvanized  
**Static Load Safety Factor:** 5:1  
**Complies With:** SMACNA HVAC-DCS  
**Wire Rope Diameter:** 2 mm



## SPECIFICATIONS

| Catalog Number | Article Number | Wire Rope Length | Wire Rope "Y" Length (YL) | A     | B    | Static Load |
|----------------|----------------|------------------|---------------------------|-------|------|-------------|
| SLK2Y300L7     | 196556         | 7m               | 0.3m                      | 42 mm | 8 mm | 440N        |
| SLK2Y500L3     | 196554         | 3m               | 0.5m                      | 42 mm | 8 mm | 440N        |

**Height (H):** 55 mm  
**Width (W):** 19 mm  
**Thickness (T):** 12.5 mm  
**Angle (a):** 90 ° Max



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

Europe

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

Europe

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

APAC

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

