

Multi-Function C-Clamp, Stainless steel, 17–30 mm Flange



CATALOG NUMBER

C30S4

FEATURES

Multi-functional beam clamp

Use with Cable/Conduit/Pipe Clamp or Square Washer for Multi-Function C-Clamp

PRODUCT ATTRIBUTES

Article Number: 336140

Material: Stainless Steel 304 (EN 1.4301)

Flange Thickness (FT): 17 - 30 mm

Hole Size (HS): 14 mm

Screw Diameter (Sc): 8

Screw Length (L): 30mm

Torque (TQ): 3 N·m

Static Load: 1100N

ADDITIONAL PRODUCT DETAILS

Setscrew must be tightened and torqued onto the sloped side of the I-beam.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

