

nVent CADDY Speed Link Y-Toggle with Eyelet Extension, 1.5 mm Wire, 0.2 m Y-Length

CATALOG NUMBER

SLD15Y200



FEATURES

Attaches to clearance holes in a variety of structures or hanging devices

Ideal for supporting lighting fixtures

Y-design provides improved stability



PRODUCT ATTRIBUTES

Article Number: 195999

Material: Steel

Finish: Electrogalvanized

Static Load Safety Factor: 5:1

Wire Rope Diameter: 1.5 mm

Wire Rope "Y" Length (YL): 0.2m


A: 39 mm

B: 5 mm

Static Load: 195N

ADDITIONAL PRODUCT DETAILS

nVent CADDY Speed Link locking device not included.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

