

Improved Cat HP J-Hook with Pedestal Clamp, 100mm dia, 22.2-28.5mm Round Pedestal

CATALOG NUMBER

CAT64HPCD1B



The Improved nVent CADDY Cat HP J-Hook with Pedestal Clamp is an innovative assembly featuring a combination of the Improved nVent CADDY Cat HP J-Hook with a Pedestal Clamp attachment. The Assembly simplifies cable management by offering quick installation to pedestals under raised floors.

Engineered for high-performance data cable management, this system supports Cat 5e, Cat 6, Cat 6A, Cat 7, and fiber optic cables with superior fill capacity and load ratings compared to most non-continuous alternatives. The Assemblies' rounded edges ensure proper bend radius support, protecting cable integrity and optimizing performance.

FEATURES

Listed for use with flexible conduit, cable or tubing

Versa-Mount Technology: Innovative attachment design provides multiple structural and installation methods for wall, ceiling, raised floors and threaded rod mounting applications

Improved design allows for optimized inventory, reducing job site scheduling risks associated with multiple SKUs

Provides optimal support for high-performance data cable—including category cable, Power over Ethernet (PoE), and fiber optic

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569



PRODUCT ATTRIBUTES

Article Number: 181229

Material: Steel

Finish: Pregalvanized

Diameter: 100 mm

Area: 9987mm²

Cable Capacity, Cat 5e: 330

Cable Capacity, Cat 6: 220

Cable Capacity, Cat 6A: 140

Pedestal Size: 19 mm Square;22.2 - 28.5 mm Round

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

