

# Multi-Function C-Clamp, Steel, Hot-dip galvanized, 17–30 mm Flange



## CATALOG NUMBER

**C30HD**

## FEATURES

Multi-functional beam clamp

Use with Cable/Conduit/Pipe Clamp or Square Washer for Multi-Function C-Clamp

## PRODUCT ATTRIBUTES

Article Number: 336110

Material: Steel

Finish: Hot-Dip Galvanized

Flange Thickness (FT): 17 - 30 mm

Hole Size (HS): 14 mm

Screw Diameter (Sc): 8

Screw Length (L): 30mm

Torque (TQ): 3 N·m

Static Load: 1100N

## ADDITIONAL PRODUCT DETAILS

Setscrew must be tightened and torqued onto the sloped side of the I-beam.



**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

