


Improved nVent CADDY Cat HP J-Hook with Strut Attachment Clip



The Improved nVent CADDY Cat HP J-Hook with Strut Attachment Clip is an innovative assembly featuring a combination of the Improved nVent CADDY Cat HP J-Hook with a Strut Attachment Clip. The Assembly simplifies cable management by offering quick installation to the open side of a strut channel.

Engineered for high-performance data cable management, this system supports Cat 5e, Cat 6, Cat 6A, Cat 7, and fiber optic cables, with superior fill capacity and load ratings compared to most non-continuous alternatives. The Assemblies' rounded edges ensure proper bend radius support, protecting cable integrity and optimizing performance.

FEATURES

Fits into Type A, B, C and D strut channels, both slotted and solid

Versa-Mount Technology: Innovative attachment design provides multiple structural and installation methods for wall, ceiling, and threaded rod mounting applications

Improved design allows for optimized inventory, reducing job site scheduling risks associated with multiple SKUs

Provides optimal support for high-performance data cable—including category cable, Power over Ethernet (PoE), and fiber optic

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569



SPECIFICATIONS

Table 1/2

Catalog Number	Article Number	Material	Finish	Diameter	Area	Cable Capacity, Cat 5e
CAT16HPESC	181022	Steel, Spring Steel	Pregalvanized, nVent CADDY Armour	25 mm	690mm ²	20
CAT21HPESC	181261	Steel, Spring Steel	Pregalvanized, nVent CADDY Armour	33.3 mm	1174mm ²	50

Catalog Number	Article Number	Material	Finish	Diameter	Area	Cable Capacity, Cat 5e
CAT32HPESC	181023	Steel, Spring Steel	Pregalvanized, nVent CADDY Armour	50 mm	2561mm ²	90

Table 2/2

Catalog Number	Article Number	Cable Capacity, Cat 6	Cable Capacity, Cat 6A	A	Static Load
CAT16HPESC	181022	15	10	10 mm	270N
CAT21HPESC	181261	40	25	10 mm	270N
CAT32HPESC	181023	60	35	10 mm	270N

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

