

Wedge Expansion Anchor Bolt

FEATURES

ICC® approved for use in cracked and uncracked concrete

Includes nut and washer


Meets NFPA® 13 as pre-qualified for seismic applications



Material: Steel
Finish: Electrogalvanized

SPECIFICATIONS

Catalog Number	Article Number	Screw Diameter (Sc)	Length 1 (L1)	Length 2 (L2)	Torque (TQ)
CSBCAB030037EG	404434	10	76 mm	44.5 mm	27 N·m
CSBCAB037550EG	404435	12	95 mm	54 mm	54 N·m
CSBCAB045050EG	404436	12	114 mm	73 mm	54 N·m
CSBCAB047562EG	404438	16	121 mm	73 mm	81 N·m
CSBCAB055050EG	404437	12	138 mm	98 mm	54 N·m
CSBCAB055075EG	404440	20	138 mm	83 mm	149 N·m
CSBCAB060062EG	404439	16	152 mm	105 mm	81 N·m
CSBCAB062575EG	404441	20	159 mm	102 mm	149 N·m



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

