

Universal Free-Stand Flat End Plate Mild Steel



Flat End plate is used to seal open side(s) of Universal Free-Stand Enclosures. The Flat End Plate provides a low profile cover and is Type 4, 12, 3R, and IP66 rated. Studs welded to the end plate eliminate bolt holes. Gasket and mounting hardware are furnished.

FEATURES

Universal Free-Stand Flat End plate is used to seal open side(s) of nVent HOFFMAN Universal Free-Stand Enclosures.

The Flat End Plate provides a low profile cover and is Type 4, 12, 3R, and IP66 rated

Studs welded to the end plate eliminate bolt holes

Gasket and mounting hardware are furnished

Material: Mild Steel
Finish: Powder Coated
Color: Gray
Color Code: ANSI 61

SPECIFICATIONS

Catalog Number	Article Number	Height	Width	Depth	Thickness
AU7218FEP	38972	1832mm	460mm	7mm	1.98mm
AU8418FEP	38973	2137mm	460mm	7mm	1.98mm
AU8424FEP	38974	2137mm	613mm	7mm	1.98mm
AU9018FEP	60455	2286mm	460mm	7mm	1.98mm
AU9024FEP	60456	2286mm	613mm	7mm	1.98mm

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.