

4G24 Twist Clip with Stud, CADDY ARMOUR, Gray, 25 mm Screw, 1.5 mm Flange, 24 mm T-Grid



CATALOG NUMBER

4G24M25

FEATURES

- Supports electrical fixtures from acoustical T-grid
- No tools required for installation
- Fast, easy and secure twist-on installation
- Designed to reduce scratching of T-grid
- Nut sold separately



PRODUCT ATTRIBUTES

Article Number: 171730

Material: Spring Steel;Steel

Finish: nVent CADDY Armour

Color: Gray

Screw Length (L): 25mm

Flange Thickness (FT): 1.5 mm

T-Grid Size: 24mm

Screw Diameter (Sc): 6

Static Load: 220N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

