

C-Channel Type E4, Perforated, 2,000 mm x 38 mm x 15.5 mm x 2 mm

CATALOG NUMBER

E420H2000PG

FEATURES

Perforated, cold rolled



PRODUCT ATTRIBUTES

Article Number: 599998

Material: Steel

Finish: Pregalvanized

Length (L): 2000mm

A: 40 mm

B: 38 mm

C: 15.5 mm

D: 50 mm

Y: 14 x 27 mm

Thickness (T): 2 mm



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

