

nVent CADDY Rod Lock Channel Nut

FEATURES

Provides fast universal attachment of threaded rod and hardware to standard strut profiles

Can be used to prefabricate assemblies which can be quickly pushed onto previously installed threaded rods

Works with slightly damaged threads and minor burrs on the threaded rod

Easy "push-to-install" design allows installers to simply push the threaded rod through the mounting hole, instantly holding it in position





Material: Cast Iron
Finish: Electrogalvanized




SPECIFICATIONS

Catalog Number	Article Number	Rod Size (RS)	B	C	D	Length (L)	Static Load
CRLSM10EG	390004	10	35 mm	19.5 mm	13.5 mm	23mm	3750N
CRLSM8EG	390003	8	35 mm	19.5 mm	13.5 mm	23mm	2750N

DIAGRAMS





WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

nVent.com/ENDD1

