

Wire Basket Tray Center Support



The nVent CADDY Wire Basket Tray Center Support is a simple and efficient way to support wire basket trays from a single threaded rod. The offset center tube helps ensure the tray is centered and secured, enhancing both structural integrity and improving project efficiency. Designed for light-duty cable support projects, installation is easy—simply hold the Center Support parallel to the tray, then turn perpendicular until you hear the Center Support lock into place.

Compatible with varying nVent CADDY Wire Basket Tray sizes, the ceiling support is precision-engineered to handle the weight of the trays with confidence. Its pre-punched design simplifies mounting with standard fasteners. Its compatibility with various finishes—including pre-galvanized, zinc electroplate, and powder coat options—adds aesthetic and functional versatility to any project.

FEATURES

Use as a central support when hanging with threaded rod

Designed to be used with the nVent CADDY Wire Basket Tray Splice Kit

Supported with 3/8 or 1/2 in threaded rod


Material: Steel
Finish: Electrogalvanized



SPECIFICATIONS

Catalog Number	Color	Height (H)	Width (W)	Length (L)	Hole Size (HS)	Unit Weight
WBTCTSPRT12		193.55 mm	41.4 mm	292.176mm	15.75 mm	1.225 kg
WBTCTSPRT4		193.55 mm	41.4 mm	105.156mm	15.75 mm	0.7 kg
WBTCTSPRT4BA	Black	193.55 mm	41.4 mm	105.156mm	15.75 mm	0.7 kg
WBTCTSPRT6		193.55 mm	41.4 mm	147.777mm	15.75 mm	0.816 kg
WBTCTSPRT8		193.55 mm	41.4 mm	190.551mm	15.75 mm	0.907 kg

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

