


# Air Baffle Without Front Panel



The air baffle without a partial front panel can be combined with a front panel that covers the complete width. It covers an empty slot to eliminate an air leak.

### FEATURES

- Air baffles eliminate air leaks from empty slots
- Cover is pushed into the guide rail

|                 |                                                                       |
|-----------------|-----------------------------------------------------------------------|
| Material:       | Aluminum                                                              |
| Product Family: | EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Inpac |
| Product Type:   | Air Baffle                                                            |
| Type:           | Without Front Panel                                                   |



### SPECIFICATIONS

| Catalog Number | Rack Height | Package Quantity | Depth | Rack Width | Works With      |
|----------------|-------------|------------------|-------|------------|-----------------|
| 34562-827      | 6U          | 1                | 220mm | 4HP        | Subracks, Cases |
| 34562-824      | 3U          | 1                | 220mm | 4HP        | Subracks, Cases |
| 34562-826      | 6U          | 1                | 160mm | 4HP        | Subracks, Cases |
| 34562-823      | 3U          | 1                | 160mm | 4HP        | Subracks, Cases |

### ADDITIONAL PRODUCT DETAILS

Air baffle for 280 mm deep and for 80 mm rear I/O boards available on request.

### WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.