


On Board Rack



Suitable for ongoing vibrations, shock, high temperatures, and high humidity.

FEATURES

For mobile railway applications

Suitable for ongoing vibrations, shock, high temperatures, and high humidity

Suitable for 1, 2, or 3 U SNCF subracks (NF F61-005, CF 60-002)

Rear side is equipped for standard connectors; crossbar can be custom-coded for the SNCF coding pins

Crossbar with integrated cable channel

Several racks can be stacked or fitted in rows

Produced using a welding process, certified to EN 15085 (CL2)

Stainless Steel welds passivated to prevent corrosion

Depth:	341.8mm
Finish:	Raw
Complies With:	SNCF NFF 61005; SNCF NFF 60002
Frame Material:	Stainless Steel
Static Load:	25kg
Product Type:	Rack



SPECIFICATIONS

Catalog Number	Rack Height	Height	Width	Package Quantity	Material	Rack Width
10170-012	6U	290mm	496.4mm	1	Stainless Steel	84HP
10170-013	6U	290mm	252.65mm	1	Stainless Steel	36HP
10170-014	3U	156.7mm	496.4mm	1	Stainless Steel	84HP
10170-015	3U	156.7mm	252.65mm	1	Stainless Steel	36HP
10170-016	9U	423.4mm	496.4mm	1	Stainless Steel	84HP
10170-017	9U	423.4mm	252.65mm	1	Stainless Steel	36HP

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.