

100T Heavy Duty Trapeze Loop Hanger



FEATURES

Recommended for the suspension of stationary non-insulated pipe lines

Designed for heavy duty trapeze installations where space is limited and attachment to structure is difficult

UL® Listed to support trapeze assembly loads of 8" pipe size

Conforms with Federal Specification WW-H-171 (Type 10), Manufacturers Standardization Society (MSS) SP-58 (Type 10)

Meets NFPA®-13 requirements for trapeze loop hangers

Material: Steel
Finish: Pregalvanized




SPECIFICATIONS

Catalog Number	Outer Diameter (OD)	A	B	C	Static Load
100T0200EG	63.5 mm	125.2 mm	60.3 mm	36.5 mm	5500N
100T0250EG	76.2 mm	143.2 mm	71.4 mm	41.3 mm	5500N
100T0300EG	92.1 mm	166.9 mm	88.9 mm	47.6 mm	5500N
100T0350EG	104.8 mm	178.1 mm	92.1 mm	47.6 mm	5500N
100T0400EG	119.1 mm	195.8 mm	101.6 mm	50.8 mm	5500N

ADDITIONAL PRODUCT DETAILS

Upper trapeze support and lower hanger must be able hold the maximum load intended for the trapeze assembly.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

