

37 Steel Eye Socket Rod Hanger

FEATURES

Joins hanger rod to a structure



Material: Steel
Finish: Pregalvanized



SPECIFICATIONS

Table 1/2

Catalog Number	Pipe Size, FM	Pipe Size, UL	NB/DN	Hole Size 1 (HS1)	Hole Size 2 (HS2)	Height (H)
0370037EG	3/4" - 4"	3/4" - 4"	19.1 - 100	12.5 mm	6.4 mm	57.2 mm
0370050EG	2 1/2" - 6"	2 1/2" - 8"	63.5 - 150	17.5 mm		69.9 mm

Table 2/2

Catalog Number	Width (W)	Static Load
0370037EG	28.6 mm	1100N
0370050EG	38.1 mm	3380N

ADDITIONAL PRODUCT DETAILS

Load rating dependent on wood structure strength.

FM® Approved for 1/2" rod size when fastened to concrete and steel only.

DIAGRAMS

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

