

510 nVent CADDY EZ Riser



The 510 nVent CADDY EZ Riser is a quick-closing pipe clamp, ideal for supporting vertical steel pipe where space is available. Ready-to-use out of the box, this solution has slotted holes to simplify assembly and eliminate loose hardware. Due to the serrated washer-head design, installers can easily assemble the EZ Riser with just a single tool.

FEATURES

Only one tool needed to tighten due to serrated washer-heads

Conforms with Federal Specification WW-H-171 (Type 8), Manufacturers Standardization Society (MSS) SP-58 (Type 8)

Material: Steel
Finish: Electrogalvanized



SPECIFICATIONS

Catalog Number	NB/DN	Outer Diameter (OD)	Hole Size (HS)	A	B	Static Load	Certifications
5100050EG	15	21 mm	11 mm	216 mm	25 mm	1100N	
5100075EG	20	27 mm	11 mm	229 mm	25 mm	1100N	
5100100EG	25	34 mm	11 mm	229 mm	25 mm	1100N	
5100125EG	32	43 mm	11 mm	240 mm	25 mm	1100N	
5100150EG	40	48 mm	11 mm	245 mm	25 mm	1100N	
5100200EG	50	60 mm	11 mm	260 mm	30 mm	1100N	ITB, UL, cUL
5100250EG	65	73 mm	11 mm	280 mm	30 mm	1735N	cUL, ITB, UL
5100300EG	80	89 mm	11 mm	298 mm	30 mm	2400N	UL, cUL, ITB
5100400EG	100	114 mm	14 mm	330 mm	38 mm	3600N	cUL, ITB, UL
5100500EG	125	141.3 mm	14 mm	368 mm	38 mm	5200N	cUL, UL
5100600EG	150	168.3 mm	14 mm	406 mm	51 mm	6900N	cUL, UL
5100800EG	200	219 mm	17 mm	464 mm	51 mm	11100N	cUL, UL
5101000EG	250	273 mm	17 mm	524 mm	51 mm	11100N	



Catalog Number	NB/DN	Outer Diameter (OD)	Hole Size (HS)	A	B	Static Load	Certifications
5101200EG	300	324 mm	17 mm	569 mm	51 mm	12000N	
5101400EG	350	356 mm	17 mm	613 mm	51 mm	12000N	
5101600EG	400	406 mm	21 mm	708 mm	64 mm	13000N	

ADDITIONAL PRODUCT DETAILS

Clamp is fitted for steel pipe and should be installed below a coupling or shear lug, with bolts torqued to recommended value.

Slotted holes and bolts for pipe sizes up to 12" only.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

