

BC200-CD Conduit to Beam Clamp



FEATURES

Eliminates offset bending conduit

Threaded hole on back


Ideal for electrical, mechanical, and HVAC applications

Material: Steel
Finish: Electrogalvanized



SPECIFICATIONS

Catalog Number	Outer Diameter (OD)	Flange Thickness (FT)	Rod Size (RS)	Torque (TQ)	Static Load	Certifications
BC200CD0B	17 - 22 mm	16 mm Max	6	4 N·m	440N	cUL, UL
BC200CD1B	19 - 25 mm	16 mm Max	6	4 N·m	440N	cUL, ITB, UL
BC200CD2B	25 - 33 mm	16 mm Max	6	4 N·m	440N	cUL, UL



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

