

100T Heavy Duty Trapeze Loop Hanger, 2" Pipe, 2 1/2" OD



CATALOG NUMBER

100T0200EG

FEATURES

Recommended for the suspension of stationary non-insulated pipe lines

Designed for heavy duty trapeze installations where space is limited and attachment to structure is difficult

UL® Listed to support trapeze assembly loads of 8" pipe size

Conforms with Federal Specification WW-H-171 (Type 10), Manufacturers Standardization Society (MSS) SP-58 (Type 10)

Meets NFPA®-13 requirements for trapeze loop hangers



PRODUCT ATTRIBUTES

Material: Steel

Finish: Pregalvanized

Pipe Size: 2" Min

Outer Diameter (OD): 63.5 mm

Rod Size (RS): 1/2"

A: 125.2 mm


B: 60.3 mm

C: 36.5 mm

Static Load: 5500N

ADDITIONAL PRODUCT DETAILS

Upper trapeze support and lower hanger must be able hold the maximum load intended for the trapeze assembly.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

