

# 315 Malleable Iron Purlin Clamp, Plain, 3/8" Rod, 1" Max Flange



## CATALOG NUMBER

**3150037PL**

## FEATURES

Attaches to lower flange of metal beams or purlins

Supports 45° flanges up to 2" long, and 90° flanges up to 1-1/2" high

Conforms with Federal Specification WW-H-171 (Type 23), Manufacturers Standardization Society ANSI®/MSS-SP-58 (Type 23)



## PRODUCT ATTRIBUTES

Material: Cast Iron

Finish: Plain

Flange Thickness (FT): 25.4 mm Max

A: 50.8 mm

B: 38.1 mm

Torque (TQ): 6.78 N·m


Pipe Size: 4" Max

Static Load: 1779N

## ADDITIONAL PRODUCT DETAILS

Setscrew must be tightened and torqued onto the sloped side of the I-beam.

Install in accordance with applicable code.



**WARNING**

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

**North America**

+1.800.753.9221  
Option 1 – Customer Care  
Option 2 – Technical  
Support

**Europe**

Netherlands:  
+31 800-0200135  
France:  
+33 800 901 793

**Europe**

Germany:  
800 1890272  
Other Countries:  
+31 13 5835404

**APAC**

Shanghai:  
+ 86 21 2412 1618/19  
Sydney:  
+61 2 9751 8500

