


CADDY ALL-IN-ONE Between-Stud Without Mud Ring, Single Box, (8) 1/2", 3/4", (3) 1/2" Knockout Sizes, w/Ground, 3 5/8"



CATALOG NUMBER

A1BF0GTC

FEATURES

Provides the flexibility to add a mud ring for non-standard drywall thicknesses

Box remains fixed in place when mud ring is removed

Pre-bent tabs on support bracket help to quickly square assembly to stud

Center marks provide easy height positioning

Includes multiple 1/2" and 3/4" in knockouts on each side of the box

Works with standard US and Canadian mud rings



PRODUCT ATTRIBUTES

Material: Steel

Finish: Pregalvanized

Knockout Sizes: (2) 12.7 mm; (8) 12.7 mm, 19.1 mm

Ground Wire Included: Yes

Box Volume: 537cm³

Stud Spacing: 406.0 - 609.6 mm

Depth (D): 92.1mm

A: 136.53 mm

B: 104.78 mm


ADDITIONAL PRODUCT DETAILS

Ground wire pigtail is 10".

24" stud spacing requires use of three mounting screws.

Use only with nVent CADDY All-in-One box assemblies.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

