

Angle Bracket, Steel, PG, 0.25" Holes



CATALOG NUMBER

AB

FEATURES

Provides an attachment for nVent CADDY Speed Link assemblies, wire, threaded rod, S-hooks, or chain from concrete or wood



PRODUCT ATTRIBUTES

Material: Steel

Finish: Pregalvanized

Hole Size 1 (HS1): 6.3 mm

Hole Size 2 (HS2): 6.3 mm


Height (H): 25.3 mm

Length (L): 25.3mm

Width (W): 19 mm

Thickness (T): 2.74 mm

Static Load: 700N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

