


Cat HP J-Hook Mod Clip with Angle Bracket, 1/2" Hole

CATALOG NUMBER

CATHPMA8



Improved nVent CADDY Cat HP Mod Clip J-Hook Bracket with Angle Bracket simplifies cable management with color-coded options for easy pathway identification and rapid attachment to various surfaces. The bracket allows for customizable cable routing configurations while ensuring compatibility with nVent CADDY Cat HP components of any size—making it a trusted choice in the field.

FEATURES

Works with nVent J-Hook Versa-Mount technology from nVent CADDY

Quickly and easily attaches to concrete, steel or composite metal decking

Integrated pin installs easily using powder-actuated or single-shot gas-actuated tools

ICC-ES ESR-2024 evaluation report available for drive pin from DEWALT® ready-to-go out of the box




PRODUCT ATTRIBUTES

Finish: nVent CADDY Armour

Material: Spring Steel

Hole Size (HS): 12 mm

Static Load: 890kg



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

