

Cat HP J-Hook Mod Clip with BC200 Beam Clamp, 1/8"–5/8" Flange



CATALOG NUMBER

CATHPMBC200

The Improved nVent CADDY Cat HP Mod Clip J-Hook with BC200 Beam Clamp eliminates the need for screws, rivets, or special tools—significantly cutting down installation time and expense. Contractors gain a secure hold on J-Hooks, boosting stability and flexibility on-site while minimizing inventory impact.

FEATURES

Easy beam flange installation

Tool-free assembly

Works with nVent J-Hook Versa-Mount technology from nVent CADDY




PRODUCT ATTRIBUTES

Finish: Electrogalvanized;nVent CADDY Armour

Material: Steel;Spring Steel

Flange Thickness (FT): 3.175 - 15.875 mm

Static Load: 445kg



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

