

URC Attachment Kit, #12 Brace, Red, 7/16" Hole, 10' Brace Length



CATALOG NUMBER

CSB2W12URC38L10

FEATURES

Attaches cable brace to structure

Two-way bracing kit with oval sleeves

Wraps around structural steel members



PRODUCT ATTRIBUTES

Brace Size: #12

Color: Red

Material: Steel

Finish: Electrogalvanized;Painted

Hole Size: 11 mm

Brace Length: 3.05 m

Cable Length: 4.2m

UL Listed Load: 1859N

ADDITIONAL PRODUCT DETAILS

FBC™ System Compatible indicates that this product has been tested, and is monitored on an ongoing basis, to assure its chemical compatibility with FlowGuard Gold®, BlazeMaster® and Corzan® piping systems and products made with TempRite® Technology.” “The FBC System Compatible Logo, FBC™, FlowGuard Gold®, BlazeMaster®, Corzan®, and TempRite® are trademarks of Lubrizol Advanced Materials, Inc. or its affiliates.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

