

Clevis Bolt Spacer, 10" Pipe

CATALOG NUMBER

CSBCS1000

FEATURES

Seismically braces the 401 Clevis Hanger series for lateral load

Retrofit ability allows the spacer to be installed after the clevis and pipe are installed

Ears easily pinch closed around the clevis hanger cross bolt with pliers

FM® Specification Tested (up to 8" Pipe Size)



PRODUCT ATTRIBUTES

Material: Steel

Finish: Electrogalvanized

Pipe Size: 10"


Width (W): 267.2 mm

Height (H): 31 mm

Thickness (T): 1.9 mm

Depth (D): 27.7mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

