


MC/AC Trapeze Support, 14-3 TO 10-2, 8X4 Cables, Shot Fire, 1/4" Rod, 12" Length

CATALOG NUMBER

MCS100TX4



The nVent CADDY MCS Trapeze (MCST) is a fast and cost-effective method for installing a wide range of MC/AC cable in overhead and trapeze installations. The MCST series eliminates the need for traditional fasteners, reducing installation time and material cost. The break-apart design feature makes it simple to field modify, providing an ideal solution for contractors looking to maximize installation efficiency.

FEATURES

Shot fire flange for direct attachment to ceiling/deck

Easy to use break-apart feature for easy field modification

Properly spaces MC/AC cable to help eliminate bundling and NEC® and CEC derating issues

Up to 50% installation time savings over traditional methods



PRODUCT ATTRIBUTES

Material: Steel

Finish: Pregalvanized

Outer Diameter (OD): 10.922 - 14.224 mm

Cable Capacity: 32


Length 1 (L1): 76.2 mm

Length 2 (L2): 304.8 mm

Height (H): 63.5 mm

ADDITIONAL PRODUCT DETAILS

Accommodates 1/4" threaded rod trapeze drops.



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

