

SK Single Piece Strut Clamp for Conduit, Steel, EG, 2" EMT, 2" Rigid/Pipe



CATALOG NUMBER

SK325I

FEATURES

One piece break apart strut clamp for EMT and Rigid conduit

Includes thread impression and captured screw



PRODUCT ATTRIBUTES



Material: Steel

Finish: Electrogalvanized

Outer Diameter (OD): 55.8 - 60.3 mm

Width (W): 32 mm

Static Load: 890N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

