

Electrical Box Mounting Strap, 24" Max Stud Spacing



CATALOG NUMBER

TEBS1624

FEATURES

Can be used as a height gauge for box center lines of 12", 15" or 18"

Pre-punched holes provide easy screw insertion

Keyholes allow simple premounting and installation of screws

Replaces multiple SKUs compared to competitor products

Marked centerline for 16" and 24" stud spacing

Ideal for use with TEB23 and CER4 for box mounting

Works with TSRBS1625 as a floor mounted box support



PRODUCT ATTRIBUTES


Material: Steel

Finish: Pregalvanized

Stud Spacing: 609.6 mm Max

Length (L): 647.7mm

Width (W): 39.1 mm



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

