


H-PSM Conduit to Flange Clip, Side Mount

FEATURES

Requires only a hammer to install

Available for EMT, rigid and aluminum conduit


Will pivot thru 360°



Orientation: Side Mount
Material: Spring Steel
Finish: nVent CADDY Armour

SPECIFICATIONS

Catalog Number	Outer Diameter (OD)	Flange Thickness (FT)	Ultimate Static Load (F)
12P24SM	22 - 30 mm	3 - 8 mm	111N
12P58SM	22 - 30 mm	8 - 14 mm	111N
12P912SM	22 - 30 mm	14 - 20 mm	111N
16P24SM	30 - 35 mm	3 - 8 mm	111N
16P58SM	30 - 35 mm	8 - 14 mm	111N
16P912SM	30 - 35 mm	14 - 20 mm	111N
8P24SM	18 - 22 mm	3 - 8 mm	111N
8P58SM	18 - 22 mm	8 - 14 mm	111N
8P912SM	18 - 22 mm	14 - 20 mm	111N



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

