


Hammer-On Flange Clip, Side Mount

FEATURES

Provides an attachment for wire, S-hooks, chain, nVent CADDY Speed Link or other assemblies to flanges and profiles

Fits most beams

Installs with just a hammer




SPECIFICATIONS

Catalog Number	Material	Finish	Flange Thickness (FT)	Hole Size (HS)	Static Load	Certifications
2H4	Spring Steel	nVent CADDY Armour	2 - 3 mm	7.1 mm	700N	ITB, UL, cUL
4H1318	Spring Steel	nVent CADDY Armour	21 - 28 mm	7.1 mm	900N	cUL, UL
4H24	Spring Steel	nVent CADDY Armour	3 - 8 mm	7.1 mm	900N	cUL, UL, CE, 4H, EM, EBC, ITB
4H24SS	Stainless Steel 301 (EN 1.4310)		3 - 8 mm	7.1 mm	620N	
4H58	Spring Steel	nVent CADDY Armour	8 - 14 mm	7.1 mm	900N	UL, CE, 4H, EM, EBC, cUL, ITB
4H58SS	Stainless Steel 301 (EN 1.4310)		8 - 14 mm	7.1 mm	620N	
4H912	Spring Steel	nVent CADDY Armour	14 - 20 mm	7.1 mm	900N	cUL, UL, CE, 4H, EM, EBC, ITB

Catalog Number	Material	Finish	Flange Thickness (FT)	Hole Size (HS)	Static Load	Certifications
4H912SS	Stainless Steel 301 (EN 1.4310)		14 - 20 mm	7.1 mm	620N	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

