

Hex Head Bolt

FEATURES


Fully threaded hexagon head bolt

Material: Steel
Finish: Electrogalvanized

SPECIFICATIONS

Catalog Number	Screw Length (L)
HSCR3710EG	25.4mm
HSCR3712EG	31.8mm
HSCR3715EG	38.1mm
HSCR5015EG	38.1mm

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper

installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

