

Independent Support Clip

FEATURES

Provides a means of independent support of fixtures

No tools required for installation

Includes mounting hardware



Material: Spring Steel
Finish: nVent CADDY Armour




SPECIFICATIONS

Catalog Number	T-Grid Size	Flange Thickness (FT)	Screw Diameter (Sc)	Screw Length (L)	Static Load	Included Components	Certifications
IDS	24mm	1.6 mm	0.25	16mm	290N	Washer-Wing Nut	UL
IDS15	23.8mm	1.6 mm	6	38.1mm	290N	Washer-Wing Nut	UL
IDS9	14mm	1.6 mm		15.9mm	290N	Washer-Wing Nut	UL
IDS95	14mm	7.9 mm		15.9mm	290N	Washer-Wing Nut	UL
IDS95LN	14mm, 24mm	7.9 mm		15.9mm	290N		
IDS95T	14mm	7.9 mm		14.3mm	290N	Pal Nut	
IDS9LN	14mm	1.6 mm		15.9mm	290N		
IDS9T	14mm	1.6 mm		14.3mm	290N	Pal Nut	
IDSLN	24mm	1.6 mm		15.9mm	290N		

Catalog Number	T-GridSize	Flange Thickness (FT)	Screw Diameter (Sc)	Screw Length (L)	Static Load	Included Components	Certifications
IDST	24mm	1.6 mm		14.3mm	290N	Pal Nut	

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

