

Lathers Channel to Rod/Wire Clip, Side Mount



FEATURES

Provides pre-leveling of channel

No tools required for installation

Use with plain rod or wire

Material: Spring Steel
Finish: nVent CADDY Armour




SPECIFICATIONS

Catalog Number	Lathers Channel Height (H)	Lathers Channel Width (W)	Wire Size	Static Load
4B15LS	38.1mm	11.1 - 15.9 mm	1 mm Min	880N
4B2LS	50.8mm	11.1 - 15.9 mm	1 mm Min	700N

ADDITIONAL PRODUCT DETAILS

4B15LS meets NYC Building Code for 280lb load rating (see PE letter in Resources tab).



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221

Option 1 – Customer Care

Option 2 – Technical

Support

Europe

Netherlands:

+31 800-0200135

France:

+33 800 901 793

Europe

Germany:

800 1890272

Other Countries:

+31 13 5835404

APAC

Shanghai:

+ 86 21 2412 1618/19

Sydney:

+61 2 9751 8500



©2026 nVent. All nVent marks and logos are owned or licensed by nVent Services GmbH or its affiliates. All other trademarks are the property of their respective owners. nVent reserves the right to change specifications without notice.

This document is system-generated.

