


nVent CADDY All-in-One Between-Stud With Removable Mud Ring, Single Box



FEATURES

Removable mud ring provides front access to the interior of the box

Box remains fixed in place when mud ring is removed

Pre-bent tabs on support bracket help to quickly square assembly to stud

Center marks provide easy height positioning

Includes multiple ½ and ¾ in knockouts on each side of the box

Material: Steel
Finish: Pregalvanized
Knockout Sizes: (2) 12.7 mm;(8) 12.7 mm, 19.1 mm



SPECIFICATIONS

Table 1/2

Catalog Number	Gang	Ground Wire Included	Box Volume	Drywall Thickness	Stud Spacing	Depth (D)
A1BF1G	1	Yes	537cm ³	15.9 mm	406.0 - 609.6 mm	92.1mm
A1BF2G	2	Yes	537cm ³	15.9 mm	406.0 - 609.6 mm	92.1mm
A1BF3G	1	Yes	537cm ³	31.6 mm	406.0 - 609.6 mm	92.1mm

Table 2/2

Catalog Number	A	B
A1BF1G	136.53 mm	104.78 mm
A1BF2G	136.53 mm	104.78 mm
A1BF3G	136.53 mm	104.78 mm


ADDITIONAL PRODUCT DETAILS

Ground wire pigtail is 10".

24" stud spacing requires use of three mounting screws.

Use only with nVent CADDY All-in-One box assemblies.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

