


nVent CADDY All-in-One Between-Stud Without Mud Ring, Multi-Box



FEATURES

Comes with multiple boxes pre-assembled for side by side power and data applications

Provides the flexibility to add a mud ring for non-standard drywall thicknesses

Box remains fixed in place when mud ring is removed

Pre-bent tabs on support bracket help to quickly square assembly to stud

Center marks provide easy height positioning

Includes multiple knockouts on each side of the box

Works with standard US and Canadian mud rings



SPECIFICATIONS

Table 1/2

Catalog Number	Material	Finish	Knockout Sizes, Box 1	Knockout Sizes, Box 2	Ground Wire Included, Box 1	Volume, Box 1
A1BF0G40N	Steel	Pregalvanized	(8) 12.7 mm, 19 mm, (3) 12.7 mm	(4) 25.4 mm, (4) 31.8 mm	Yes	537cm ³

Table 2/2


Catalog Number	Ground Wire Included, Box 2	Volume, Box 2	Stud Spacing	Depth (D)	A	B
A1BF0G40N	No	688cm ³	406.4 - 609.6 mm	92.1mm	136.5 mm	104.8 mm

ADDITIONAL PRODUCT DETAILS

Ground wire pigtail is 10".

24" stud spacing requires use of three mounting screws.

Use only with nVent CADDY All-in-One box assemblies.



+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Germany:
800 1890272
Other Countries:
+31 13 5835404

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500

